

Garant
Clamp toolholder, right-hand, Shank / insert size: 25/12mm

Order data

Order number	250006 25/12
GTIN	4045197861542
Item class	21T

Technical description

Overall length L	150 mm
Head length L ₁	33 mm
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Clamping claw	259038 4
Shim	259031 22
Shank size	25 mm
Shim screw	259025 6
Screw for clamping claw	259021 1
ISO code toolholder	MCLNR/L 2525M12
Functional width L ₄	32 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw Type 4	259038 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 22	259031 22
Shim screw Type 6	259025 6
Screw for clamping claw Type 1	259021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500