

Garant
Clamp toolholder, left-hand, Shank / insert size: 32/19mm

Order data

Order number	250007 32/19
GTIN	4045197861641
Item class	21T

Technical description

Shim	259031 24
Functional width L ₄	40 mm
Head length L ₁	40 mm
Screw for clamping claw	259021 5
Clamping claw	259038 5
Shim screw	259025 8
Insert size	19 mm
ISO code toolholder	MCLNR/L 3232P19
Shank size	32 mm
Overall length L	170 mm
suitable indexable insert	CN.. 1906..
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Clamping claw Type 5	259038 5
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Screw for clamping claw Type 5	259021 5
Shim Type 24	259031 24
Shim screw Type 8	259025 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600