

Garant**Burr Z9 very coarse (NF/Alu), Carbide, Type: AS0616****Order data**

Order number	540709 AS0616
GTIN	4045197522436
Item class	51D

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape AS cylindrical(ZYAS), with end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 6 mm

Head length: 16 mm

Overall length: 50 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Z9
Toothing grit designation	very coarse (NF/Alu)
Shape	AS0616
Overall length	50 mm
Shape description	Cylindrical with end cut
Head Ø	6 mm

Shank Ø	6 mm
Head length	16 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		