

**Garant**
**Burr Z9 very coarse (NF/Alu), Carbide, Type: D1009**

**Order data**

Order number	540709 D1009
GTIN	4045197555564
Item class	51D

**Description**
**Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape D ball**(KUD).

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Ball

Head Ø: 10 mm

Head length: 9 mm

Overall length: 49 mm

Shank Ø: 6 mm

**Technical description**

Shape description	Ball
Tooth type abbreviation	Z9
Shape	D1009
Toothing grit designation	very coarse (NF/Alu)
Head Ø	10 mm
Overall length	49 mm

Shank Ø	6 mm
Head length	9 mm
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		