

Garant
Lever lock toolholder, left-hand, Shank / insert size: 32/15mm

Order data

Order number	251107 32/15
GTIN	4045197862006
Item class	21T

Technical description

Shim punches pack	259047 4
ISO code toolholder	PSBNR/L 3232P15
suitable indexable insert	SN.. 1506..
Overall length L	170 mm
Lever screw	259018 11
Shank size	32 mm
Head length L ₁	32 mm
Shim	259031 37
Insert size	15 mm
Shim pins pack	259044 6
Functional width L ₄	27 mm
Lever	259015 12
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500