

Garant

GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 12mm



Order data

Order number	123026 12
GTIN	4045197846914
Item class	11E

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Standard	Manufacturer's standard
Nominal Ø D_c	12 mm
Number of cutting edges Z	2
Shank Ø D_s	12 mm
Feed f in steel < 1100 N/mm ²	0.2 mm/rev.
Tolerance nominal Ø	h7
recommended maximum drilling depth L_2	96 mm
Overall length L	162 mm

Flute length L_c	114 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	8×D
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, to 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	195 m/min	P
Steel < 750 N/mm ²	suitable	150 m/min	P
Steel < 900 N/mm ²	suitable	135 m/min	P
Steel < 1100 N/mm ²	suitable	125 m/min	P
Steel < 1400 N/mm ²	suitable	80 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	65 m/min	M
GG	suitable	120 m/min	K
GGG	suitable	115 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		