

Garant**Support cabinet, for insert size length×width: 800X600mm****Order data**

Order number	431050 800X600
GTIN	4045197512369
Item class	41C

Description**Version:**

Sturdy welded construction including levelling fittings. Uneven floors can be compensated using height compensation screws.

Support cabinet, casing made from sheet steel, with swing-door (including storage shelf) and/or drawers depending on size, including GARANT locking system. Paint finish of the shell RAL 9006 aluminium white, front faces RAL 5011 steel blue.

Application:

The natural granite tables No. 430190 - 430500 are mounted on pre-determined points (steel ball inserts).

- **For plates up to 630×630 mm. For setting up on workbenches and the like, adjustable screw jacks No. 373500 are most suitable.**
- **The support jacks are adjustable for height and allows the table to be levelled (3-point contact and 2 support screws as protection against tipping)**

Fitted with:

Door height (left): 480 mm

Note:

For vibration-absorbing machine mounts, please order 4× No. 086002 size 850.

Cylinder lock: modular barrel

Support cabinet height: 720 mm

Support cabinet width: 550 mm

Support cabinet depth: 560 mm

Height of support cabinet incl. bearing sets: 780 mm

Load capacity, distributed: 500 kg
Weight: 51 kg

Technical description

Weight	51 kg
Electronic locking system can be retrofitted	yes
Number of doors	1
Support cabinet height	720 mm
Load capacity, distributed	500 kg
suitable for worktop size length×width	800×600 mm
Support cabinet width	550 mm
Support cabinet depth	560 mm
maximum working height (top face of the granite table)	900 mm
Height of support cabinet incl. bearing sets	780 mm
Drawer/pull-out shelf load capacity	100 kg
Drawer runner extension (partial/full extension)	90 %
Height adjustment	25 mm
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel
Type of product	Sub-frame