



## Grinding and inspection vice with spindle, Jaw width A: 125mm



### Order data

Order number	363550 125
GTIN	4045197313584
Item class	38F

### Description

**Version:**

- **Hardened steel; precision ground all round.**
- Working on 4 different faces** (front, rear, and side faces).  
With horizontal **ground Vee profile**.

**Function:**

**Pull-down system** – The movable jaw is pulled down by the resulting clamping force; no lifting of the component or vibration during machining.

**Application:**

For **machining and inspection true to gauge**.

**Accuracy:**

Within **0.003 mm** / 100 mm (system accuracy).

**Supplied with:**

Operating crank handle.

### Technical description

Weight	14.5 kg
Overall length a	300 mm
maximum clamping range b	160 mm
Jaw width A	125 mm
Jaw height C	43 mm

Overall width B	125 mm
Type of product	Checking vice