


Grinding and inspection vice with quick adjustment, Jaw width A: 70mm**Order data**

Order number	363230 70
GTIN	4045197295811
Item class	38F

Description**Version:**

Ground Vee grooves.

All-steel, through hardened and **precision ground all round** for 4-face machining.

With quick adjustment (no spindle).

Application:

For **machining and inspection true to gauge.**

Accuracy:

Within **0.005 mm** / 100 mm.

Supplied with:

Sturdy **case.**

Technical description

Overall length a	160 mm
maximum clamping range b	80 mm
Base body height G	62 mm
Weight	3 kg
Jaw width A	70 mm
Jaw height C	30 mm
Overall width B	70 mm

Type of product

Checking vice

Accessories

Spare clamping unit complete for jaw width A 70 mm

363235 70