



Side milling cutter with thread Width $a_p = 6$ mm, $\varnothing D: 63$ _ mm

Order data

Order number	218544 63_
GTIN	4045197849564
Item class	210

Description

Version:

Side milling cutters of robust special steel for reduced vibration.

Application:

For milling grooves and slots.

Achievable base of the slot = 176° (not flat).

Note:

Side milling cutters available up to $\varnothing D = 200$ mm.

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit shank No. **674248 size TX15**.

Through-coolant: false

Tool exchange: PowerCard

ISO code indexable insert: SN..1203

Pack of insert screws: 219950 (TX15; 2.2 Nm)

Technical description

ISO code indexable insert	SN..1203
Pack of insert screws	219950 (TX15; 2.2 Nm)
Through-coolant	no
Tool material	
Tool exchange	PowerCard
Shank type	
Width a_p	6 mm
Machining strategy	
Norm	
Type of product	

