

Garant
Burr Z9 very coarse (NF/Alu), Carbide, Type: D1614

Order data

Order number	540709 D1614
GTIN	4045197679819
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape D ball**(KUD).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Ball

Head Ø: 16 mm

Head length: 14 mm

Overall length: 54 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Z9
Shape	D1614
Toothing grit designation	very coarse (NF/Alu)
Shape description	Ball
Head Ø	16 mm
Overall length	54 mm

Shank Ø	6 mm
Head length	14 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		