



## HOLEX CleverDrill HSS jobber drill N, uncoated, Ø DC h8 (mm or inch): 1,45



### Order data

Order number	114030 1,45
GTIN	4045197850263
Item class	12B

### Description

#### Version:

**HOLEX CleverDrill:** Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

#### Recommendation:

#### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

#### Note:

**Successor product for No. 114050 and No. 114160.**

Size 13.2 – 20: With stepped shank Ø 12.7 mm.

Through-coolant: no

Standard: DIN 338

Tolerance nominal Ø: h8

Point angle: 130°

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 15.8 mm

Flute length  $L_c$ : 18 mm

Overall length L: 40 mm

Shank Ø  $D_s$ : 1.45 mm

Feed f in steel < 750 N/mm<sup>2</sup>: 0.03 mm/rev.

### Technical description

Feed f in steel < 750 N/mm <sup>2</sup>	0.03 mm/rev.
recommended maximum drilling depth $L_2$	15.8 mm
Tolerance nominal Ø	h8

Overall length L	40 mm
Flute length L <sub>c</sub>	18 mm
Standard	DIN 338
Shank Ø D <sub>s</sub>	1.45 mm
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	1.45 mm
Point angle	130 °
Series	HOLEX CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Shank	Plain shank
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	60 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	32 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K

## Data sheet

CuZn	suitable	40 m/min	N
Oil	suitable		
wet maximum	suitable		