



Solid carbide mini milling cutter, uncoated, Ø e8 DC: 16mm



Order data

Order number	202266 16
GTIN	4045197864901
Item class	12X

Description

Version:

Shank similar to **DIN 635 HB**.

Save on regrinding costs:

It is cheaper to use solid carbide mini milling cutters to the wear limit than to regrind them.

Technical description

Tolerance nominal Ø	e8
Feed f_z for slot milling in steel < 750 N/mm ²	0.08 mm
No. of teeth Z	3
Flute length L_c	18 mm
Shank form	HB
Cutting edge Ø D_c	16 mm
Shank	HB with h6
Direction of infeed	horizontal, oblique and vertical
Shank Ø D_s	16 mm
Overall length L	65 mm
Feed f_z for side milling in steel < 750 N/mm ²	0.13 mm
Helix angle	45 degrees
Corner chamfer angle	90 degrees

Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	170 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	100 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	45 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable only under restricted conditions	55 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	Suitable		
dry	suitable only under restricted conditions		
Air	Suitable		

