

**Garant**
**Burr Z7 – medium, diamond cut, Carbide, Type: D1210**

**Order data**

Order number	540200 D1210
GTIN	4045197155009
Item class	51D

**Description**
**Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 12 mm

 Head length L<sub>1</sub>: 10 mm

Overall length: 51 mm

Shank Ø: 6 mm

**Technical description**

Head length L <sub>1</sub>	10 mm
Shape description	ball
Overall length	51 mm
Type of cut	staggered teeth
Toothing grit designation	medium
Shape	D1210

Tooth type abbreviation	Z7
Shank Ø	6 mm
Head Ø	12 mm
Tool material	Carbide
Type of product	Burr