

**Garant**
**Burr Z7 – medium, diamond cut, Carbide, Type: AS1625**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 540200 AS1625 |
| GTIN         | 4045197154910 |
| Item class   | 51D           |

**Description**
**Version:**

Shank Ø 6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape AS (ZYAS), with end cut.**

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical with end cut

Head Ø: 16 mm

Head length L<sub>1</sub>: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

**Technical description**

|                            |                          |
|----------------------------|--------------------------|
| Shape description          | Cylindrical with end cut |
| Type of cut                | staggered teeth          |
| Shape                      | AS1625                   |
| Toothing grit designation  | medium                   |
| Head length L <sub>1</sub> | 25 mm                    |
| Overall length             | 65 mm                    |

|                         |         |
|-------------------------|---------|
| Tooth type abbreviation | Z7      |
| Shank Ø                 | 6 mm    |
| Head Ø                  | 16 mm   |
| Tool material           | Carbide |
| Type of product         | Burr    |