

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: L1020

Order data

Order number	540200 L1020
GTIN	4045197155146
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round cone shape** (KEL).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round cone

Head Ø: 10 mm

 Head length L₁: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Overall length	60 mm
Shape description	round cone
Shape	L1020
Type of cut	staggered teeth
Head Ø	10 mm
Head length L ₁	20 mm

Toothing grit designation	medium
Tooth type abbreviation	Z7
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr