

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: C1225



Order data

Order number	540200 C1225
GTIN	4045197154958
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 12 mm

Head length L₁: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Z7
Overall length	65 mm
Head length L ₁	25 mm
Shape	C1225
Type of cut	staggered teeth
Head Ø	12 mm

Toothing grit designation	medium
Shape description	ball nose
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr