



Flap disc (special ZA) glass fibre pad flat, 115 mm Ø, Grit: 80

Order data

Order number	565300 80
GTIN	4045197157782
Item class	51M

Description

Version:

Roughing grinding discs with cloth flaps coating with Zirconium Aluminium Oxide (ZA) or ceramic grit on backing pads of steel, plastic or glass fibre. Circumferential speed **ideally 50-60 m/s**, max. 80 m/s. Gentle, cool grinding with high self-sharpening effect (no clogging); low vibration and low force working, low noise level.

· **Flat shape – for surface grinding – and weld dressing with approach angles 0 -15°.**

Flap disc with glass fibre pad and polyester fabric with greatly above-average working life.

Application:

Universal for **all steels**, even for use on **hardened edges**.

Grinding medium code: ZA

Iron, sulphur and chlorine constituents: < 0.1 %

optimised for material: Steel

optimised for material: INOX

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

Technical description

Backing pad	
Bonding	
maximum circumferential speed	80 m/s
recommended circumferential speed	m/s
Grit structure	
recommended approach angle	degrees
Grinding media	

Grinding medium code	ZA
Adapter	
optimised for material	Steel
optimised for material	INOX
Iron, sulphur and chlorine constituents	< 0.1 %
See-through grinding	
Shape	
suitable for quick-change system	
abrasive, cooling coating	
Grinding media backing	
Propulsive equipment	
Thread	
Product name attribute	115 mm Ø
maximum speed	rpm
Type of product	