

Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 7,5mm

Order data

| | |
|--------------|---------------|
| Order number | 202292 7,5 |
| GTIN | 4045197866066 |
| Item class | 11X |

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Technical description

| | |
|---|----------------------------------|
| Direction of infeed | horizontal, oblique and vertical |
| Cutting edge Ø D _c | 7.5 mm |
| Shank Ø D _s | 8 mm |
| Overall length L | 63 mm |
| No. of teeth Z | 3 |
| Shank | DIN 6535 HA to h6 |
| Tolerance nominal Ø | e8 |
| Overhang length L ₁ incl. recess | 27 mm |
| Recess Ø D ₁ | 7.3 mm |
| Feed f _z for side milling in steel < 750 N/mm ² | 0.05 mm |
| Feed f _z for slot milling in steel < 750 N/mm ² | 0.04 mm |
| Flute length L _c | 19 mm |
| Helix angle | 45 degrees |
| Corner chamfer angle | 90 degrees |

| | |
|---|-----------------------------|
| Coating | AlCrN |
| Tool material | Solid carbide |
| Standard | DIN 6527 |
| Type | N |
| Cutting width a_e for milling operation | 0.5×D for side milling |
| Cutting width a_e for milling operation | Full slot cutting depth 1×D |
| Through-coolant | no |
| Colour ring | without |
| Type of product | End / face mill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 280 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 200 m/min | N |
| Steel < 500 N/mm ² | suitable | 120 m/min | P |
| Steel < 750 N/mm ² | suitable | 110 m/min | P |
| Steel < 900 N/mm ² | suitable | 100 m/min | P |
| Steel < 1100 N/mm ² | suitable | 70 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 60 m/min | P |
| INOX < 900 N/mm ² | suitable | 70 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 50 m/min | M |
| GG(G) | suitable | 90 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

| | |
|------------------------|---|
| dry | suitable only under restricted conditions |
| Air Services | suitable |
| Shank grinding Type HB | 129100 HB |