


**Garant**
**Abrasive cap holder, Head Ø, head length, shape: 1319C**

**Order data**

Order number	553100 1319C
GTIN	4045197330536
Item class	51E

**Description**
**Version:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

**Slotted, resilient rubber body** with steel shank.

**Application:**

Used mostly in tool making for finishing where access is difficult.

**Suitable for :**

Abrasive caps No. 553035 – 553328.

Shank Ø: 3 mm

maximum speed: 35000 min<sup>-1</sup>

**Technical description**

Head Ø	13 mm
maximum speed	35000 min <sup>-1</sup>
Shank Ø	3 mm
Head length	19 mm
Type of product	Abrasive cap holders

