


**Solid carbide milling cutter, AlCrN, Ø e8 DC: 5,5mm**

**Order data**

Order number	202296 5,5
GTIN	4045197866400
Item class	12X

**Description**
**Version:**

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

**Technical description**

Shank	DIN 6535 HB to h6
Cutting edge $\varnothing D_c$	5.5 mm
Flute length $L_c$	13 mm
Direction of infeed	horizontal, oblique and vertical
Feed $f_z$ for slot milling in steel $< 750 \text{ N/mm}^2$	0.03 mm
Feed $f_z$ for side milling in steel $< 750 \text{ N/mm}^2$	0.04 mm
Shank form	HB
No. of teeth Z	3
Shank $\varnothing D_s$	6 mm
Overall length L	57 mm
Corner chamfer width at $45^\circ$	0.2 mm
Tolerance nominal $\varnothing$	e8
Helix angle	45 degrees
Corner chamfer angle	45 degrees

Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	50 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	60 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	M
GG(G)	suitable	75 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		

Air

suitable