



## Small cutting disc PREMIUM\*\*\* EXTRA THIN, Disc Ø: 75mm



### Order data

Order number	563050 75
GTIN	9003172992709
Item class	53T

### Description

#### Version:

Extremely thin **small cutting disc** for use with **pneumatic or electric straight grinders**, ideal for use in confined work spaces. For use with mandrel No. 563070.

Easy cutting version for quick low-burr cutting.

#### Version of the advertising text:

Extremely thin **small cutting disc** for use with **pneumatic or electric straight grinders**, ideal for use in confined work spaces.

#### Specification:

##### A60R-BFXA.

#### Note:

The disc thickness should be at least 20% of the material thickness to be cut.

### Technical description

Shape description	flat
maximum speed	20300 min <sup>-1</sup>
Disc thickness	1 mm

Bore Ø	10 mm
Specification	A60R-BFXA
Disc Ø	75 mm
for material thicknesses	3 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	Steel
Propulsive equipment	Straight die grinder
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		

Uni	suitable only under restricted conditions
dry	suitable

---

## Accessories

Clamping mandrel for small cutting disc suitable for bore Ø 10 mm	563070 10
---	-----------