

**Garant**
**Machine tap for wire thread inserts HSS-E-PM, TiCN, EG-M: EG-M6**

**Order data**

Order number	133550 EG-M6
GTIN	4045197862051
Item class	11H

**Description**
**Version:**

Tap to **DIN 40435** (similar to DIN 371 / DIN 376).

Achieves outstanding tool life, due to high-quality substrate and TiCN coating. For wide application range of different materials.

**Application:**

For production of AC mounting thread to metric ISO threads **DIN 8140** for **STI** (Screw Thread Insert) wire thread inserts.

**Note:**

Please ensure without fail the correct **tapping drill Ø** (see table)!

Tool material: HSS E PM

Standard: DIN 40435

Tolerance class: 6H mod.

Thread pitch: 1 mm

Overall length L: 90 mm

Shank Ø D<sub>s</sub>: 8 mm

Shank square □: 6.2 mm

Tapping hole Ø: 6.3 mm

**Technical description**

Thread Ø	6 mm
Tolerance class	6H mod.
Thread pitch	1 mm
Overall length L	90 mm
Standard	DIN 40435

Number of cutting edges Z	3
Tapping hole Ø	6.3 mm
Shank Ø D <sub>s</sub>	8 mm
Tool material	HSS E PM
Number of clamping slots	3
Shank square □	6.2 mm
Thread depth	18 mm
Thread size	M6
Coating	TiCN
Thread type	EG-M
Flank angle	60 degrees
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap