

Garant
GARANT Master INOX solid carbide milling cutter HPC, TiAlN, Ø h10 DC: 20mm

Order data

Order number	203006 20
GTIN	4045197851833
Item class	11X

Description
Version:

For **roughing and finishing**.

HPC milling cutter with **newly developed high-performance coating** for **outstanding tool life** and **optimum metal removal rate** in a very wide range of stainless steels. **Greater oxidation resistance** and **high-temperature hardness**.

Can be used at **high cutting speeds**, particularly suitable even for TOOLOX®.

Advantage:

Particularly low vibration running.

Technical description

Corner chamfer width at 45°	0.35 mm
Tolerance nominal Ø	h10
Cutting edge Ø D _c	20 mm
Direction of infeed	horizontal, oblique and vertical
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.07 mm
Feed f _z for side milling in INOX > 900 N/mm ²	0.08 mm
Overhang length L ₁ incl. recess	70 mm
Flute length L _c	38 mm
Shank Ø D _s	20 mm
Overall length L	126 mm

Recess $\varnothing D_1$	19.5 mm
No. of teeth Z	4
Shank	DIN 6535 HB to h6
Helix angle	40 degrees
Corner chamfer angle	45 degrees
Series	Master INOX
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable	115 m/min	P
Steel < 50 HRC	suitable	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	85 m/min	M

wet maximum	suitable
wet minimum	suitable
dry	Suitable only under restricted conditions
Air	suitable