

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: D1009

Order data

| | |
|--------------|---------------|
| Order number | 540350 D1009 |
| GTIN | 4045197222442 |
| Item class | 51D |

Description
Version:

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Shank length 200 mm (can be cut to length).

Shank Ø 6 mm. **Shape D ball**(KUD).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Do not start the machine until the burr is inside the component.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 10 mm

Head length: 9 mm

Overall length: 209 mm

Shank Ø: 6 mm

Technical description

| | |
|---------------------------|------------|
| Overall length | 209 mm |
| Shape | Ball shape |
| Toothing grit designation | medium |
| Head Ø | 10 mm |
| Tooth type abbreviation | Z7 |

| | |
|-------------------|-----------------|
| Type of cut | staggered teeth |
| Shape description | ball |
| Shank Ø | 6 mm |
| Head length | 9 mm |
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |