

Burr, coated Z7 - medium, diamond cut, Carbide TiAlN, Type: F1630



Order data

Order number	540260 F1630
GTIN	4027497455881
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). Round arch shape (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round arch

Head Ø: 16 mm

Head length L₁: 30 mm Overall length: 70 mm

Shank Ø: 6 mm

Technical description

Shape	F1630
Head Ø	16 mm
Toothing grit designation	medium
Tooth type abbreviation	Z7

Head length L ₁	30 mm
Type of cut	staggered teeth
Shape description	round arch
Overall length	70 mm
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAlN
Type of product	Burr