

Garant**Air Cleaning Point, Type: M****Order data**

Order number	986000 M
GTIN	4045197866837
Item class	96U

Description**Version:**

Sturdy and robust cabinet of sheet steel with pneumatically driven extraction system and collection container. Operation of the extraction is performed by a foot pedal at the front. With castors and push handle at the rear for ease of transport.

All you need for operation is a compressed-air connection in the workshop.

Application:

For easy and thorough cleaning of workpieces and tools, using compressed air. Dust, chips, oils and liquids are extracted and deposited in the collection container.

Supplied with:

With GARANT compressed air gun No. 080123 size AIR, hose and Easyfix compressed air gun holder No. 955750 size 1, Easyfix plastic box No. 955790 size 74.

Colour:

RAL 7016 anthracite.

Note:

Spare filter mat can be found under No. 986001 at www.hoffmann-group.com 2 spare filter mats No. 986001 size 1 are required for replacement.

Technical description

Height	1300 mm
Compressed air connection	DN 7.2
Width	1050 mm
Type	M
Drip catch volume	40 l
Depth	450 mm
Working height	870 mm
Weight	90 kg
Type of product	Cleaning station

Accessories

Spare filter mat for Air Cleaning Point Type 1	986001 1
--	----------