



Burr, coated Z7 – medium, diamond cut, Carbide TiAlN, Type: D1210



Order data

Order number	540260 D1210
GTIN	4027497455867
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAlN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball

Head Ø: 12 mm

Head length L₁: 10 mm

Overall length: 51 mm

Shank Ø: 6 mm

Technical description

Type of cut	staggered teeth
Shape	D1210
Overall length	51 mm
Head Ø	12 mm

Shape description	ball
Toothing grit designation	medium
Tooth type abbreviation	Z7
Head length L ₁	10 mm
Shank Ø	6 mm
Tool material	Carbide TiAlN
Coating	TiAlN
Type of product	Burr