

**Garant****TCMT 16T308, Grade: HB7010-1****Order data**

Order number	260958 HB7010-1
GTIN	4045197852878
Item class	21G

**Description**

TCMT 16T308 HB7010-1 Grade: HB7010-1  
Chip breaker: SS  
Cutting depth  $a_p$ : 0.2 - 1.5 mm  
Feed  $f$ : 0.05 - 0.2 mm/rev.  
Cutting speed  $v_c$  main application: 150 - 500 m/min

**Technical description**

Chip breaker	SS
Cutting depth $a_p$	0.2 - 1.5 mm
Cutting speed $v_c$ main application	150 - 500 m/min
Grade	HB7010-1
Corner radius	0.8 mm
Main application	P
Feed $f$	0.05 - 0.2 mm/rev.
Cutting conditions	continuous

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Type of product	Indexable insert for turning