

Garant

Solid carbide torus cutter, uncoated, \varnothing h6 DC / R1: 10/3,0mm



Order data

Order number	206192 10/3,0
GTIN	4045197853127
Item class	11X

Description

Version:

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Tolerances:

· Corner radius

$R_1 = 0.5$ tolerance ± 0.02 .

$R_1 > 0.5 - 1.5$ tolerance ± 0.03 .

$R_1 > 1.5$ tolerance ± 0.05 .

Dimensions to manufacturer's standard.

Technical description

Shank	DIN 6535 HA to h6
Overhang length L_1 incl. recess	58 mm
Flute length L_c	16 mm
Corner radius R_1	3 mm
Recess $\varnothing D_1$	9.2 mm
No. of teeth Z	3
Balance quality with shank	G 2.5 with HA
Cutting edge $\varnothing D_c$	10 mm
Feed f_z for copy milling in short-chipping aluminium	0.05 mm
Overall length L	100 mm

Shank $\varnothing D_s$	10 mm
Feed f_z for side milling in short-chipping aluminium	0.05 mm
Helix angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Tolerance nominal \varnothing	h6
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.3×D for side milling
Through-coolant	no
Shank tolerance	h6
Colour ring	yellow
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	130 m/min	N
Aluminium (short chipping)	suitable	100 m/min	N
Alu > 10% Si	suitable	80 m/min	N
PMMA acrylic	Suitable	130 m/min	N
PE-HD	Suitable	90 m/min	N
PA 66	Suitable	100 m/min	N
PEEK	Suitable	90 m/min	N
PF 31	Suitable	80 m/min	N
Cu	Suitable	70 m/min	N
CuZn	Suitable	90 m/min	N

wet maximum	suitable
wet minimum	Suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable only under restricted conditions
Services	
Shank grinding Type HB	129100 HB