

**DC.T 070202, Grade: PDL025****Order data**

Order number	260381 PDL025
GTIN	4960664757787
Item class	25E

Description

DC.T 070202 PDL025 Grade: PDL025
Chip breaker: MFP-SK
Tolerance: G
Cutting depth a_p : 0.5 - 2.5 mm
Feed f : 0.03 - 0.15 mm/rev.
Cutting speed v_c main application: 100 - 300 m/min

Technical description

Cutting conditions	slightly interrupted
Corner radius	0.2 mm
Chip breaker	MFP-SK
Main application	N
Cutting speed v_c main application	100 - 300 m/min
Cutting depth a_p	0.5 - 2.5 mm
Grade	PDL025

Feed f	0.03 - 0.15 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCGT 070202
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning