

**Garant**
**Solid carbide reamer HPC blind hole, TiAlN, Nominal  $\varnothing$  DC: 5mm**

**Order data**

Order number	164351 5
GTIN	4045197852786
Item class	10N

**Description**
**IMPORTANT: item is configurable**

Nominal  $\varnothing$  D<sub>c</sub>: 5 mm

$\varnothing$  range: 4.71 - 5.2 mm, Intervall: 0,001

**Version:**

**Version suitable for NC** with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short, straight flutes.

**Application:**

For **HPC/HSC reaming** of **blind holes**.

**Note:**
**NEW GENERATION AVAILABLE!**
**Recommended successor product is No. 164425.**

Application for type of drilling: for blind holes

Number of cutting edges Z: 4

$\varnothing$  range: 4.71 - 5.2 mm

Flute length L<sub>c</sub>: 12 mm

Overhang L<sub>1</sub>: 34 mm

Overall length L: 75 mm

Number of cutting edges Z: 4

Shank  $\varnothing$  D<sub>s</sub>: 6 mm

**Technical description**

Flute length L <sub>c</sub>	12 mm
-----------------------------	-------

Overall length L	75 mm
Nominal $\varnothing D_c$	5 mm
Shank tolerance	h6
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.06 mm/rev.
Number of cutting edges Z	4
$\varnothing$ range	4.71 - 5.2 mm
Overhang L <sub>1</sub>	34 mm
Shank $\varnothing D_s$	6 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA to h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	blue
Type of product	Phillips bit

## User data

	Suitability	V <sub>c</sub>	ISO code
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		