

**Garant**
**Solid carbide reamer HPC blind hole, TiAlN, Nominal Ø DC: 9mm**

**Order data**

Order number	164351 9
GTIN	4045197853264
Item class	10N

**Description**
**IMPORTANT: item is configurable**

Ø range: 8.71 - 9.2 mm, Intervall: 0,001

Nominal Ø D<sub>C</sub>: 9 mm

**Version:**

**Version suitable for NC** with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short, straight flutes.

**Application:**

For **HPC/HSC reaming** of **blind holes**.

**Note:**
**NEW GENERATION AVAILABLE!**
**Recommended successor product is No. 164425.**

Application for type of drilling: for blind holes

Number of cutting edges Z: 6

Ø range: 8.71 - 9.2 mm

Flute length L<sub>c</sub>: 20 mm

Overhang L<sub>1</sub>: 54 mm

Overall length L: 100 mm

Number of cutting edges Z: 6

Shank Ø D<sub>s</sub>: 10 mm

**Technical description**

Ø range	8.71 - 9.2 mm
---------	---------------

Nominal $\varnothing D_c$	9 mm
Number of cutting edges Z	6
Overall length L	100 mm
Flute length $L_c$	20 mm
Shank tolerance	h6
Overhang $L_1$	54 mm
Feed f in stainless steel $< 900 \text{ N/mm}^2$	0.15 mm/rev.
Shank $\varnothing D_s$	10 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA to h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	blue
Type of product	Phillips bit

## User data

	Suitability	$V_c$	ISO code
INOX $< 900 \text{ N/mm}^2$	suitable	30 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		