

**Garant**
**Solid carbide reamer HPC blind hole, TiAlN, Nominal  $\varnothing$  DC: 14mm**

**Order data**

Order number	164351 14
GTIN	4045197853349
Item class	10N

**Description**
**IMPORTANT: item is configurable**

 Nominal  $\varnothing$  D<sub>c</sub>: 14 mm

 $\varnothing$  range: 13.21 - 14.2 mm, Intervall: 0,001

**Version:**

**Version suitable for NC** with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short, straight flutes.

**Application:**

 For **HPC/HSC reaming** of **blind holes**.

**Note:**
**NEW GENERATION AVAILABLE!**
**Recommended successor product is No. 164425.**

Application for type of drilling: for blind holes

Number of cutting edges Z: 6

 $\varnothing$  range: 13.21 - 14.2 mm

 Flute length L<sub>c</sub>: 22 mm

 Overhang L<sub>1</sub>: 78 mm

Overall length L: 130 mm

Number of cutting edges Z: 6

 Shank  $\varnothing$  D<sub>s</sub>: 14 mm

**Technical description**

Nominal $\varnothing$ D <sub>c</sub>	14 mm
--------------------------------------	-------

Shank $\varnothing D_s$	14 mm
$\varnothing$ range	13.21 - 14.2 mm
Overhang $L_1$	78 mm
Shank tolerance	h6
Number of cutting edges Z	6
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.2 mm/rev.
Flute length $L_c$	22 mm
Overall length L	130 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA to h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	blue
Type of product	Phillips bit

## User data

	Suitability	$V_c$	ISO code
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		