

Garant
Slim hydraulic chuck, SK 30 A = 80, Clamping range $\varnothing D_1$: 6 mm

Order data

Order number	302091 6
GTIN	4045197868510
Item class	31A

Description
Version:

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With Balluffchip bore.**
- **Axial length adjustment facility.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.**
For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302180.

$\varnothing D_2$: 16 mm

$\varnothing D_3$: 16.3 mm

External $\varnothing D$: 40 mm

L_2 : 41 mm

Technical description

$\varnothing D_3$	16.3 mm
Clamping $\varnothing D_1$	6 mm

Ø D ₂	16 mm
L ₂	41 mm
External Ø D	40 mm
Adapter	SK 30 A = 80
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

Pull stud stud sealed, form A suitable for steep tapers 30	308610 30
Pull-stud 60° sealed suitable for steep tapers 30	308780 30
Pull stud 45° sealed suitable for steep tapers 30	308760 30
Pull stud 60° sealed suitable for steep tapers 30	308785 30