

Garant
Slim hydraulic chuck, SK 30 A = 80, Clamping range \varnothing D1: 8 mm

Order data

Order number	302091 8
GTIN	4045197868527
Item class	31A

Description
Version:

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With Balluffchip bore.**
- **Axial length adjustment facility.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.** For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302180.

\varnothing D₂: 14 mm

\varnothing D₃: 18.3 mm

External \varnothing D: 40 mm

L₂: 41 mm

Technical description

L ₂	41 mm
\varnothing D ₂	14 mm

Clamping $\varnothing D_1$	8 mm
External $\varnothing D$	40 mm
$\varnothing D_3$	18.3 mm
Adapter	SK 30 A = 80
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

Pull stud 60° sealed suitable for steep tapers 30	308785 30
Pull stud stud sealed, form A suitable for steep tapers 30	308610 30
Pull-stud 60° sealed suitable for steep tapers 30	308780 30
Pull stud 45° sealed suitable for steep tapers 30	308760 30