

Garant
Slim hydraulic chuck, SK 40 A = 160, Clamping range \varnothing D1: 10mm

Order data

Order number	302095 10
GTIN	4045197868640
Item class	31A

Description
Version:

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.** For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302187.

Technical description

Overhang dimension A	160 mm
L ₂	121 mm
\varnothing D ₂	20 mm
\varnothing D ₃	37.1 mm
External \varnothing D	49.5 mm

Clamping $\varnothing D_1$	10 mm
Adapter	SK 40 A = 160
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studForm A suitable for steep tapers 40	308600 40
	308802 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Pull studsealed suitable for steep tapers 40

308660 40

Pull studsealed suitable for steep tapers 40

308635 40

Special pull stud with no internal threadsealed suitable for steep tapers 40

308700 40

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40

308615 40

ER chuck key1/2 inch socket for ER collet chuck 40

309700 40

Pull stud, 18CrNiMo7Form A suitable for steep tapers 40

308605 40

Pull stud 90°sealed suitable for steep tapers 40

308790 40

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40

308820 40

Pull studsealed, form B suitable for steep tapers 40

308650 40

ER chuck key for ER collet chuck 40

309680 40