

Garant
**GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN,
 Ø f8 DC: 13,7 mm**

Order data

Order number	202402 13,7
GTIN	4045197853721
Item class	11X

Description
Version:

Corner radii matched to DIN specifications for **drive keyways**.

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to 1×D into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Tolerance nominal Ø: f8

No. of teeth Z: 3

Helix angle: 38 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HB to h6

No. of teeth Z: 3

Flute length L_c : 14 mm

Overall length L: 75 mm

Shank Ø D_s : 14 mm

Corner rounding r_v : 0.32 mm

Feed f_z for slot milling in steel < 900 N/mm²: 0.08 mm

Technical description

No. of teeth Z	3
Flute length L_c	14 mm
Shank	DIN 6535 HB to h6

Feed f_z for side milling in steel < 900 N/mm ²	0.1 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.08 mm
Shank $\varnothing D_s$	14 mm
Overall length L	75 mm
Direction of infeed	horizontal, oblique and vertical
Cutting edge $\varnothing D_c$	13.7 mm
Tolerance nominal \varnothing	f8
Helix angle	38 degrees
Corner rounding r_v	0.32 mm
Series	GARANT Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Cutting width a_e for milling operation	0.4×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End mill