

Garant
HiPer-Drill base body, 10×D, Ø DC: 15mm

Order data

Order number	231617 15
GTIN	4045197868169
Item class	21S

Description
Version:

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

Polished flutes.

Application:

For stationary and rotating use. For holes up to IT9 accuracy.

Note:

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

Reduce feed rates f by 10 % and v_c values by 30 %.

For process reliability when using the drill, initial pilot drilling to 1.5×D with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Technical description

Dia. range D_c	15 - 15.99 mm
Shank length L_s	50 mm
Reach L_1	160 mm
Shank Ø D_s	20 mm

Clamping screw	231999 8IP (0.9 Nm)
Series	HiPer-Drill
Number of cutting edges Z	2
Overall length L	237 mm
Version	10xD
Shank	ISO 9766
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 0,9 N·m	211750 0,9
Torx Plus® screw Drive 8IP	231999 8IP