

Garant**Burr Z FINE – very fine, Carbide, Type: A0820****Order data**

| | |
|--------------|---------------|
| Order number | 540440 A0820 |
| GTIN | 4045197679901 |
| Item class | 51D |

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape A (ZYA), without end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|-----------------------------|
| Shape | A0820 |
| Tooth type abbreviation | Z FINE |
| Shape description | Cylindrical without end cut |
| Overall length | 60 mm |
| Head Ø | 8 mm |
| Toothing grit designation | very fine |
| Shank Ø | 6 mm |
| Head length | 20 mm |
| Series | Tooth configuration Z FINE |
| Tool material | Carbide |

Type of product

Burr

User data

| | Suitability | V_c | ISO code |
|--------------------------------|--------------------|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |