



Burr, coated Z7 – medium, diamond cut, Carbide TiAlN, Type: G1225



Order data

Order number	540260 G1225
GTIN	4027497043422
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAlN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Gothic arch shape** (SPG).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Pointed

Head Ø: 12 mm

Head length L₁: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Head length L ₁	25 mm
Tooth type abbreviation	Z7
Shape description	Pointed
Shape	G1225

Type of cut	staggered teeth
Head Ø	12 mm
Overall length	65 mm
Toothing grit designation	medium
Shank Ø	6 mm
Tool material	Carbide TiAlN
Coating	TiAlN
Type of product	Burr