



Soft Job Abrasive flap disc (ZA), Ø 50.8 mm, Grit: 60



Order data

Order number	554030 60
GTIN	9003172469843
Item class	53T

Description

Version:

The Roloc™, Combidisc® CDR **quick-change system** with a plastic external thread permits safe abrasive tool changing “with a single twist of the wrist” in a very short time.

Very flexible version with stand-up strips and strip overlaps **for extremely gentle even grinding.**

Compared to conventional grinding discs, **mini-flap discs** with abrasive strips arranged at a very steep angle offer a **longer working life, more flexible grinding characteristics** and a **more even surface finish** (roughness value) down to the wear limit.

Application:

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

Note:

Roloc™ bristle discs can be found from No. 573511 onwards.

Technical description

Grit	60
Disc Ø	50.8 mm
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Grinding media backing	Plastic pad

Product name attribute	Ø 50.8 mm
Thread	Roloc™ quick-change system
maximum speed	20000 min ⁻¹
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		

Accessories

Rubber backing pad shank Ø 6 mmhard External Ø 50 mm	554089 50
Rubber backing pad shank Ø 6 mmsoft External Ø 50 mm	554091 50
Rubber backing pad shank Ø 6 mmmedium External Ø 50 mm	554092 50
	554093 50

Rubber backing pad shank \varnothing 6 mm medium hard External
 \varnothing 50 mm

Plastic backing pad shank \varnothing 6 mm External \varnothing 50 mm

554090 50