

**Garant**
**Face mill arbor with cooling channel bore, HSK-A 63 A = 130, Spigot Ø d1: 16mm**

**Order data**

Order number	306566 16
GTIN	4045197870162
Item class	31A

**Description**
**Version:**

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

With **cooling channel bores.**

**Application:**

For clamping shell end mills and milling cutter heads.

**Supplied with:**

Lock screw.

**Optional extras:**

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

**Technical description**

Spigot Ø d <sub>1</sub>	16 mm
Suitable toggle spanner No. 309840	16
External Ø D	38 mm
Overhang dimension A	130 mm
Spare milling cutter lock screw No. 309860 / 309861	16

Milling mandrel length $L_4$	17 mm
Clamping $\varnothing D_1$	16 mm
Adapter	HSK-A 63 A = 130
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

---

## Accessories

Milling cutter lock screw for mandrel $\varnothing 16$ mm	309860 16
Toggle spanner for mandrel $\varnothing 16$ mm	309840 16