

Garant
Solid carbide NC machine reamer Configurable, TiAlN, Nominal Ø DC: 3,2mm

Order data

Order number	164344 3,2
GTIN	4045197854483
Item class	10N

Description
Version:

Version suitable for NC DIN 8093-2 with straight shank Ø for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. This ensures **very high concentricity** and **process reliability**,

The use of GARANT-NC reamers eliminates the need to procure special collets. With long flutes and left-hand helix.

Ramers finish ground to match your specification.

Application:

For reaming through holes, as the chips are evacuated in the cutting direction. Lead taper is suitable also for blind holes.

Note:

For H7 fit see No. 164340 and 164341.

Technical description

Ø range	3.01 - 3.35 mm
Feed f in steel < 1100 N/mm ²	0.12 mm/rev.
Shank tolerance	h6
Nominal Ø D _c	3.2 mm
Overall length L	65 mm
Flute length L _c	18 mm
Shank Ø D _s	4 mm
Overhang L ₁	37 mm

Number of cutting edges Z	6
Reaming oversize in diameter	0.05 - 0.1 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 8093
Through-coolant	no
Shank	DIN 6535 HA to h6
Application for type of drilling	for through hole
Colour ring	green
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	30 m/min	N
Alu > 10% Si	suitable only under restricted conditions	25 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	25 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable	10 m/min	P
INOX < 900 N/mm ²	suitable	15 m/min	M
INOX > 900 N/mm ²	suitable	12 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	10 m/min	S
GG(G)	suitable	10 m/min	K
CuZn	suitable	25 m/min	N
Uni	suitable		

wet maximum

suitable