

Garant
Deep hole drill HSS-E, TiAlN, Ø DC h8: 1,5mm

Order data

Order number	116063 1,5
GTIN	4045197870773
Item class	11B

Description
Version:

Significantly **strengthened core** without taper.

Precision ground point.

With **specially shaped slots**. Designed for deep holes up to 10×D and materials with critical chip formation characteristics.

With **TiAlN coating** for long tool lives.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Technical description

Shank Ø D _s	1.5 mm
Tolerance nominal Ø	h8
Standard	DIN 340
Overall length L	70 mm
Flute length L _c	45 mm
Nominal Ø D _c	1.5 mm
Feed f in steel < 750 N/mm ²	0.03 mm/rev.
Number of cutting edges Z	2
recommended maximum drilling depth L ₂	42.8 mm

Point angle	130 degrees
Shank	Plain shank
Coating	TiAlN
Tool material	HSS E
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	87 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm ²	suitable	31 m/min	P
Steel < 750 N/mm ²	suitable	23 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Ti > 850 N/mm ²	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
Oil	suitable		
wet maximum	suitable		