




Abrasive sleeve holder, slit, shank \varnothing 6 mm, Head \varnothing ×head length: 30X20mm



Order data

| | |
|--------------|---------------|
| Order number | 553600 30X20 |
| GTIN | 4045197240194 |
| Item class | 52E |

Description

Version:

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

Technical description

| | |
|---------------------|-------------------------|
| minimum speed | 13000 min ⁻¹ |
| maximum speed | 19100 min ⁻¹ |
| Head \varnothing | 30 mm |
| Head length | 20 mm |
| Shape description | cylindrical |
| Shank \varnothing | 6 mm |
| Backing material | resilient rubber body |
| Type of product | Tool sleeve carrier |