

**HOLEX®**
**Tap wrench, adjustable, Type: 0**

**Order data**

Order number	148400 0
GTIN	4045197854872
Item class	12L

**Description**
**Version:**

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

**Standard use:**

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 2 - 5 mm

for hand taps DIN 352: M1 – M8

for hand reamer Ø DIN 206: 2.5 - 6.5 mm

Overall length: 125 mm

**Technical description**

Capacity □	2 - 5 mm
Overall length	125 mm
for hand reamer Ø DIN 206	2.5 - 6.5 mm
for hand taps DIN 352	M1 – M8
Norm	DIN 1814