



## Burr Z9 – very coarse (NF/Alu), Carbide, Type: D1210

### Order data

Order number	543709 D1210
GTIN	4045197522375
Item class	51D

### Description

#### Version:

Extra sturdy shank with Ø 8 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

#### Application:

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 8 mm

Tooth type abbreviation: Z9

Shape description: Ball

Head Ø: 12 mm

Head length: 10 mm

Overall length: 50 mm

### Technical description

Propulsive equipment	
Coating	
Long shank	
Machining application	
Tool material	Carbide
Type of product	

