


**Abrasive sleeve holder, slit, shank  $\varnothing$  6 mm, Head  $\varnothing$ ×head length: 60X30mm****Order data**

Order number	553600 60X30
GTIN	4045197240224
Item class	52E

**Description****Version:**

Slotted, resilient rubber body with steel shank. Ground outer face for best concentricity.

**Technical description**

maximum speed	9500 min <sup>-1</sup>
minimum speed	6500 min <sup>-1</sup>
Head $\varnothing$	60 mm
Head length	30 mm
Shape description	cylindrical
Shank $\varnothing$	6 mm
Backing material	resilient rubber body
Type of product	Tool sleeve carrier