

Garant**Mini burr Z5 – fine, Carbide, Type: M0311****Order data**

Order number	546800 M0311
GTIN	4045197156679
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	M0311
Toothing grit designation	fine
Shape description	pointed cone
Overall length	40 mm
Tooth type abbreviation	Z5
Head \varnothing	3 mm
Shank \varnothing	3 mm
Head length	11 mm
Series	Tooth configuration Z5
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		